



Shoprider Europe SA
 ZAE Robert Steichen
 5, rue Bommel | L-4940
 Hautcharage
 Luxembourg
 Tél: +352 26 65 65 77
 www.shoprider.eu

Shoprider Europe offers you a complete mobility package incorporating world class quality, design, reliability and service.

A WORLD PATENTED NEW MODEL 889XLS(B)N w/ Cabin (14" Tire) SPECIFICATION

			w/ Lockable Box	w/o Lockable Box
Overall Dimensions: L ¹ x W x H		mm(in)	2260(89) x 730(28.7) x 1640(65)	1600(63) x 730(28.7) x 1640(65)
Number, Size of Tires		Front	2 x 14" (Black, Pneumatic)	
		Rear	2 x 14" (Black, Pneumatic)	
Total Weight (w/ 75Ah Batteries, Seat, etc.)	(w/ doors)	kg(lb)	194(427)	182(400)
	(w/o doors)	kg(lb)	175(385)	163(359)
Max. Carrying Weight including Single User Weight (on the level road) and Max. Loading Weight 25kg (55lb) of Lockable Box		kg(lb)	160(352)	
Weight of Cabin		kg(lb)	55(121)	
Battery Capacity		_V_Ah x Pcs	12V 50/75Ah (SLA) or 75Ah (GEL) x 2 Option	
Charger		Amp	4A / 8A (Off-Board) Option	
Output Power of Motor (Reference Only)		W(hp)	1350(1.8)	
Max. Speed ² (on the level road), based on the individual request		kph(mph)	Approx. 13~14(8~8.8)	
Safe Climbing Angle ³ , Max. Single User Weight		°(%), kg(lbs)	Shown as illustration.	
Range ⁴ (After the 75Ah battery and mechanical moving parts fully break in, test by 115kg User Weight including Dummy)		km(mile)	40~42(25~26.3) *Range varies with the weight of occupant and other factors	
Turning Radius		mm(in)	1780(70)	
Handle Bar Type		Type	Delta	
Suspension		Y/N	Y	
High / Low Speed		Y/N	Y	
Emergency Hand Brake		Y/N	Option(889XLSN w/ Cabin) / Y(889XLSBN w/ Cabin)	
Wiper, External / Internal Rear View Mirror		Y/N	Option	
Extra Front / Rear Bumper		Y/N	Option	
External Headlight		Y/N	Option	
Noise Isolation, Lockable Box		Y/N	Option	

Shoprider Europe reserves all rights to change the wording and specification without prior notice.

Data shown above is based on the time when tested.

Please make sure that you are physically fit to operate this unit. Consult your dealer/doctor for advice.


*1. Include the Floor Panel.

*2. For your safety, speed must be reduced when turning.

*3. When proceeding up any incline, please move your seat to the most forward position or if you have the deluxe seat, make sure that it is in the 90 degree (upright) position.

*4. The actual driving range varies with the factors shown as below.

- | | |
|----------------------------|-------------------------|
| (1) the weight of occupant | (5) ambient temperature |
| (2) level ground/gradient | (6) the way of driving |
| (3) battery conditions | (7) terrain |
| (4) type of charger | (8) etc. |



Ver : 2010.07.27/A4

WARNING!

